

# Rittal – The System.

Faster – better – everywhere.



## AS 4050.807 Spiralni sveder

State: 6.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.807 - Spiralni sveder

Strojni spiralni sveder za obdelovalne centre Perforex BC in rezkalne terminale Perforex Milling Terminals MT S.

## Features

|                           |   |
|---------------------------|---|
| Št. Modela                | AS 4050.807   |
| Zasnova                   | HSS<br>TiN prevleka   |
| Opis izdelka              | Strojni spiralni sveder za obdelovalni center Perforex BC in rezkalni terminal Perforex MT. |
| Premer                    | 8,5 mm  |
| Za model št.              | 4050107<br>4050108<br>4050230   |
| Obdelovalni material      | Steel<br>Stainless steel<br>Aluminium<br>Plastic<br>Copper                                  |
| Paketi                    | 10 pc(s).   |
| Neto teža                 | 0,41 kg   |
| Bruto teža                | 0,42 kg   |
| Carinska tarifna številka | 82051000  |
| ETIM 9                    | EC000945  |
| ETIM 8                    | EC000945  |
| ECLASS 8.0                | 36609207  |
| Opis izdelka              | Twist drill A002, 8. 5mm, packs of 10   |