

Rittal – The System.

Faster – better – everywhere.



AS 4050.887

Rezalnik krožnih navojev

State: 27.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.887 - Rezalnik krožnih navojev

Rezkar za rezanje metričnih navojev za obdelovalne centre Perforex BC in rezkalne terminale Perforex Milling Terminal MT.

Features

Št. Modela	AS 4050.887
Opis izdelka	Rezkar za rezanje metričnih navojev za obdelovalni center Perforex BC in rezkalni terminal Perforex MT.
Tehnični podatki	Premer gredi 12 mm Premer reza 10 mm Razmak 1,5 mm Stranski kot 60° Dolžina reza 20 mm Celotna dolžina 85 mm
Za navoje	M12 - M64
Standardi	DIN 13-1 metrični ISO navoj
Obdelovalni material	Steel Stainless steel Cast aluminium Plastic Copper
Paketi	1 pc(s).
Neto teža	0,124 kg
Bruto teža	0,124 kg
Carinska tarifna številka	82077031
ETIM 9	EC000945
ETIM 8	EC000945
ECLASS 8.0	36609211
Opis izdelka	Circular thread milling cutter, 10x1.5, 12 mm