

# Rittal – The System.

Faster – better – everywhere.



## TE 7888.510

## Omrežni nosilec TE 8000

State: 21.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TE 7888.510 - Omrežni nosilec TE 8000

TE 8000 IT enclosure with glazed door, prepared for individual interior installation.

## Features

Št. Modela	TE 7888.510
Zasnova	s stranskimi ploščami
Prednosti	Brez okvirja Optimalna dostopnost Enostavno razstavljanje in tudi enostavna namestitvev Zamenljiv tečaj vrat
Material	Jeklena pločevina Steklena vrata: enoslojno varnostno steklo, 3 mm
Površinska obdelava	Montažni okvir: Temeljni premaz Plošče ohišja: prašno barvano
General colour	RAL 7035
Barva	RAL 7035
Obseg dobave	Samostoječi 482,6 mm (19") montažni okvirji, spredaj in zadaj, z nastavljivo globino Steklena sprednja vrata, vključno s 130° tečajem, okrasnim ročajem in varnostno ključavnico 3524 E Vrata iz jeklene pločevine na zadnji strani, vključno s 130° tečajem, varnostna ključavnica 3524 E Osnovni okvir z največjim izrezom (za opsijsko postavitvev z modularnimi ploščami) Strešna plošča s skritim izrezom za vhod kablov in opsijskim ventilatorjem 4 nivelirne noge, M10 (priložene) 4 distančniki, 20 mm (priloženi) za dvig strešne plošče Stranske plošče, možnost zaklepanja, vključno z varnostno ključavnico 3524 E
Mere	Širina: 600 mm Višina: 2.000 mm Globina: 800 mm

# Features

Enote	42 U
Enote	42 U
Prosti montažni prostor do višine 482,6 mm (19"), spredaj/zadaj	130 mm / 130 mm /
Razdalja med nivoji (kot je dobavljeno)	495 mm
Nosilnost	4.000 N
Razred zaščite po IEC 60 529	IP 20
Osnovni material	Sheet steel
Paketi	1 pc(s).
Neto teža	88,5 kg
Bruto teža	96,5 kg
Carinska tarifna številka	94032080
ETIM 9	EC002499
ECLASS 8.0	27180207
Opis izdelka	TE Network enclosure TE 8000, WHD: 600x2000x800 mm, 42 U, With glazed door

# Approvals

Explanations

Declaration of conformity