


**Rittal – The System.**

Faster – better – everywhere.



**AS 4055.080**

**Ročni hidravlični komplet  
prebijalnikov, M16 - M40**

State: 22.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.080 - Ročni hidravlični komplet prebijalnikov, M16 - M40

Manual hydraulic punch in a practical set with hole punches for sheet steel. Maximum machinable material thickness 2 or 3 mm.

## Features

Št. Modela	AS 4055.080
Zasnova	Z glavo valja, ki je nagnjena pod kotom 90° in se vrti za 360°
Prednosti	Podaljšajte življenjsko dobo orodja z vgrajenim nadtlaknim ventilom Luknjači, hidravlični luknjači in pribor za izdelavo okroglih, kvadratnih in pravokotnih izrezov v jeklu in nerjavnem jeklu
Obseg dobave	Ročni hidravlični prebijalnik 5 luknjačev z razdelilnikom, tridelno Hidravlični vijak Ø 19 mm Hidravlični vijak Ø 9,5 / 19 mm Pilotni sveder HSS Ø 10 mm Komplet distančnih tulcev (3-delni) Plastični kovček
Obdelovalni material	Sheet steel
Največja debelina obdelovalnega materiala, jeklena pločevina	2 mm 2 mm 2 mm 3 mm 3 mm
Ø prebijača	16,2 mm 20,4 mm 25,4 mm 32,5 mm 40,5 mm
Za navoje	M16 M20 M25 M32 M40

# Features

Paketi	1 pc(s).
Neto teža	4,1 kg
Bruto teža	4,16 kg
Carinska tarifna številka	84678900
ETIM 9	EC002121
ETIM 8	EC002121
ECLASS 8.0	21049046
Opis izdelka	Hand hydraulic punch set 90° M16,20,25,32,40 mm