

Rittal – The System.

Faster – better – everywhere.



AS 4055.116

Splitter hole punch, round

State: 3.9.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.116 - Splitter hole punch, round for stainless steel, round, with triple splitting

For punching round cut-outs

Features

Model No.	AS 4055.116
Design	With triple splitting
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	Female dies Male dies
Machinable material	Stainless steel
Maximum machinable material thickness, stainless steel	2 mm
Ø punch	16,2 mm
For threads	M16
Note	When operating with wrenches, tension screws with ball bearings should be used.
Suitable for hydraulic bolt order number	4055.665
Tension screw (Ø x L)	11.1 x 60 mm
Hydraulic tension screw Ø	11,1 mm 19 cm
Packs of	1 pc(s).
Net weight	0.043
Gross weight	0.059
Customs tariff number	82073010
EAN	4028177807983

Features

ETIM 9	EC000156
ETIM 8	EC000156
ECLASS 8.0	21049047