

# Rittal – The System.

Faster – better – everywhere.



## TX 7888.831

# Omrežni nosilec TX CableNet

State: 21.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TX 7888.831 - Omrežni nosilec TX CableNet s prezračevanimi vrati

Nova raven upravljanja kablov: TX CableNet združuje dolgoletne izkušnje na področju IT ohišij, ki izpolnjujejo vse zahteve glede funkcionalnosti in kakovosti, pripravljene pa so tudi za individualno notranjo opremo.



## Features

Št. Modela	TX 7888.831
Zasnova	2. generacija Prezračevano s stranskimi ploščami
Prednosti	New roof plate concept: Optimised use of the entire enclosure volume with the enclosure cabling plus optional integration of a fan module Učinkovit koncept okvirja za individualno konfiguracijo Stranske plošče, pritrjene z vijaki za hiter dostop 482.6 mm (19") mounting angles, front and rear, adjustable in the depth Obsežna ponudba pribora za notranjo konfiguracijo po meri
Material	Streha: jeklena pločevina, 1,5 mm Okvir ohišja: jeklena pločevina, 1,5 mm Vrata: jeklena pločevina, 1,2 mm 482,6 mm (19") montažni kotniki: jeklena pločevina, 2 mm Stranska plošča: jeklena pločevina, 1,2 mm
Površinska obdelava	Okvir ohišja: temeljni premaz Plošče ohišja: Temeljni premaz, prašno barvano
Barva	RAL 7035

# Features

Obseg dobave	Ohišje z prezračevanimi sprednjimi in zadnjimi vrati Enclosure frame with 482.6 mm (19") mounting angles, front and rear Stranske plošče Screw-fastened roof plate with concealed cable entry on both sides across the entire enclosure depth plus a central, concealed cut-out for easy integration of a fan module.
Mere	Širina: 800 mm Višina: 2.000 mm Globina: 1.000 mm
Enote	42 U
Razdalja med nivoji (kot je dobavljeno)	645 mm
Zasnova	with side panels
Design doors	Prezračevano
Zasnova zadnjih vrat	Vrata iz jeklene pločevine, enodelna, prezračevana
Zasnova sprednjih vrat	Vrata iz jeklene pločevine, enodelna, prezračevana Površina prezračevanja približno 78 % perforirana
Nosilnost	5000 N
Osnovni material	Sheet steel
Paketi	1 pc(s).
Neto teža	117,5 kg
Bruto teža	118,5 kg
Carinska tarifna številka	94032080
ETIM 9	EC002499
ETIM 8	EC002499
ECLASS 8.0	27180207
Opis izdelka	TX CableNet network rack, 800x2000x1000 mm, 42 U, vented, RAL 7035

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

---