

Rittal – The System.

Faster – better – everywhere.



DK 7998.107

RiMatrix S

State: 25.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7998.107 - RiMatrix S Standardna soba

The standardised data centre is assembled at your premises within the context of hot aisle / cold aisle containment.



Features

Št. Modela	DK 7998.107
Prednosti	Izboljšana energetska učinkovitost Hladilna pregrada je kombinacija vrat in strehe, ki omogoča enakomerno ločevanje vročega in hladnega zraka
Obseg dobave	Nasveti in izračun dobe vračanja naložbe Dostava in integracija v infrastrukturo stranke Zagon in primopredaja Dokumentacija, usposabljanje in navodila Telefonska linija za pomoč in storitve/servisne pogodbe Natančno prilegajoča se zadrževalna oprema za hodnike
Globina odmika	7.000 mm
Višina odmika	2.722 mm
Širina odmika	4.774 mm
Klimatska naprava (ZUCS)	120 kW + 20 kW n+2 redundant
Število glavnih nizkonapetostnih razdelilnikov	2
Št. PDU Basic enot	28
Serverracks (600x2000x1200mm)	12

Features

Kombinirano omrežno/strežniško ohišje (800 x 2000 x 1200 mm)	2
Design burglar protection	Yes
Sistem za vlaženje in razvlaževanje	opcijsko
Sistem za gašenje požara v sobi	opcijsko
Design UPS	2 x (60 kW + 20 kW) n+1 redundant
Mere	Širina: 4.839 mm Višina: 2.750 mm Globina: 7.070 mm
Paketi	1 pc(s).
Carinska tarifna številka	73089059
ETIM 9	EC002499
ECLASS 8.0	27180207
Opis izdelka	DK RiMatrix S Standard room, Double 6
