

Rittal – The System.

Faster – better – everywhere.



TS 8126.235

Side panel, screw-fastened, sheet steel

State: 28.8.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8126.235 - Side panel, screw-fastened, sheet steel for TS, TS IT

Side panels, screw-fastened, sheet steel, for TS.

Features

| | |
|-------------------------------------|--|
| Model No. | TS 8126.235 |
| Benefits | Automatic potential equalisation and higher EMC protection due to enclosure panel holders with earthing insert Easy positioning with the location aid Earthing bolt with contact surface |
| Material | Sheet steel, 1.5 mm |
| Surface finish | Dipcoat-primed, powder-coated on the outside |
| Colour | RAL 7035 |
| Supply includes | Assembly parts |
| Note | Enclosure panel holders may optionally be fitted from the inside or outside of the enclosure Area available for population: External dimension – 100 mm |
| To fit | Enclosure type: TS TS IT Height: 2,200 mm Depth: 600 mm |
| IP protection category to IEC 60529 | IP 55 |
| Basic material | Sheet steel |
| Packs of | 2 pc(s). |
| Net weight | 29 |
| Gross weight | 32 |
| Customs tariff number | 94039910 |
| EAN | 4028177213425 |

Features

| | |
|-----------------|----------|
| E-Number Sweden | E7282535 |
| ETIM 9 | EC002524 |
| ECLASS 8.0 | 27182101 |

Tender text

Side panel, screw-fastened, for TS

Easy positioning on the frame with the location aid.

The enclosure panel holders with earthing insert ensure automatic potential equalisation and higher EMC protection.

They may optionally be fitted from the inside or outside of the enclosure.

When using TS side panel hinges an opening angle of 180° is possible.

Material: 1.5 mm sheet steel

Area available for population:

External dimension 100 mm

Protection category: IP 55

Surface finish:

Dipcoat-primed,
powder-coated in textured RAL 7035
on the outside

For enclosure dimensions: H: 2200 mm D: 600 mm