

# Rittal – The System.

Faster – better – everywhere.



## TS 8284.500

## Povezovalni sistemi TS 8

State: 4.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8284.500 - Povezovalni sistemi TS 8

The TS 8 sheet steel baying system, with its symmetrical profile in the width and depth, offers a significant space gain, plus simple interior installation. This likewise ensures bayability from all sides. Additionally, the integral, automatic potential equalisation of all enclosure panels and the triple surface treatment ensure optimum safety.



## Features

|                     |  |
|---------------------|--|
| Št. Modela          | TS 8284.500  |
| Material            | Okvir ohišja: jeklena pločevina, 1,5 mm<br>Streha: jeklena pločevina, 1,5 mm<br>Vrata: jeklena pločevina, 2,0 mm<br>Zadnja plošča: jeklena pločevina, 1,5 mm<br>Plošče z uvodnicami: jeklena pločevina, 1,5 mm<br>Montažna plošča: jeklena pločevina, 3,0 mm |
| Površinska obdelava | Okvir ohišja: temeljni premaz<br>Vrata, streha in zadnja plošča: temeljni premaz, prašno barvana zunanost, teksturirana barva<br>Montažna plošča in plošče z uvodnicami: pocinkano   |
| Barva               | RAL 7035   |

# Features

|                              |   |
|------------------------------|---|
| Obseg dobave                 | Okvir ohišja<br>Vrata<br>Zapiranje vrat pri enokrilih ohišjih, možnost zamenjave na nasprotno stran<br>Strešna plošča<br>Zadnja plošča<br>4 očesni vijaki<br>Ključavnica: 3 mm dvojna ključavnica<br>Kabelske uvodnice<br>Montažna plošča<br>2 luknjani tirnici TS 18 x 38 mm |
| Mere                         | Širina: 1.200 mm<br>Višina: 1.800 mm<br>Globina: 400 mm   |
| Mere montažne plošče (Š x V) | 1.099 mm x 1.696 mm   |
| Razred zaščite po IEC 60 529 | IP 55   |
| Razred zaščite NEMA          | NEMA 1<br>NEMA 12   |
| Tipna ocena po UL 50E        | Type 1<br>Type 12   |
| IK koda                      | IK09  |
| Število vrat                 | 2   |
| Osnovni material             | Sheet steel   |
| Paketi                       | 1 pc(s).  |
| Neto teža                    | 162,07 kg   |
| Bruto teža                   | 170,6 kg  |
| Carinska tarifna številka    | 94032080  |
| ETIM 9                       | EC000261  |
| ECLASS 8.0                   | 27180101  |
| Opis izdelka                 | TS Bayed enclosure system, WHD: 1200x1800x400 mm, Sheet steel, with mounting plate, two doors at the front  |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | Bureau Veritas<br>DNV-GL<br>Lloyds Register of Shipping<br>UL + C-UL (listed)           |
| Certificates | Surface finish  |
| Explanations | Manufacturer's declaration<br>Declaration of conformity<br>Declaration of conformity UK |

---