

Rittal – The System.

Faster – better – everywhere.



TS 8406.510

Povezovalni sistemi TS 8

State: 4.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8406.510 - Povezovalni sistemi TS 8

The TS 8 sheet steel baying system, with its symmetrical profile in the width and depth, offers a significant space gain, plus simple interior installation. This likewise ensures bayability from all sides. Additionally, the integral, automatic potential equalisation of all enclosure panels and the triple surface treatment ensure optimum safety.



Features

Št. Modela	TS 8406.510
Material	Okvir ohišja: jeklena pločevina, 1,5 mm Streha: jeklena pločevina, 1,5 mm Vrata: jeklena pločevina, 2,0 mm Zadnja plošča: jeklena pločevina, 1,5 mm
Površinska obdelava	Okvir ohišja: temeljni premaz Vrata, streha in zadnja plošča: temeljni premaz, prašno barvana zunanost, teksturirana barva
Barva	RAL 7035
Obseg dobave	Okvir ohišja Vrata Zapiranje vrat pri enokrilnih ohišjih, možnost zamenjave na nasprotno stran Strešna plošča Zadnja plošča 4 očesni vijaki Ključavnica: 3 mm dvojna ključavnica 2 podporna trakova, nameščena v globino ohišja
Mere	Širina: 400 mm Višina: 2.000 mm Globina: 600 mm

Features

Razred zaščite po IEC 60 529	IP 55 in conjunction with side panels and gland plates
Razred zaščite NEMA	NEMA 12 in conjunction with side panels and gland plates
Tipaska ocena po UL 50E	Type 1 Type 12
IK koda	IK09
Število vrat	1
2 supportstrips in depth	Yes
Osnovni material	Sheet steel
Paketi	1 pc(s).
Neto teža	51,7 kg
Bruto teža	55,6 kg
Carinska tarifna številka	94032080
ETIM 9	EC000261
ECLASS 8.0	27180101
Opis izdelka	TS Bayed enclosure system, WHD: 400x2000x600 mm, sheet steel, without mounting plate, single door at the front

Approvals

Approvals	Bureau Veritas DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Certificates	Surface finish
Explanations	Manufacturer's declaration Declaration of conformity Declaration of conformity UK