

**Rittal – The System.**

Faster – better – everywhere.



**IT 5302.042**

**482.6 mm (19") cable link, depth-  
variable**

State: 26.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# IT 5302.042 - 482.6 mm (19") cable link, depth-variable

Within the 482.6 mm (19") mounting level, the cable link provides an integrated cable routing option between the front and rear mounting levels inside an enclosure.

## Features

Št. Modela	IT 5302.042
Prednosti	Cable entry at the front via brush strip for thermal partitioning of the cable entry zone Direct cable routing between the patch level and component with rear installation, optimum cable routing with switch mounted at the rear Fully depth-variable with versatile, infinitely adjustable extension of the cable link Prevents incorrect airflow by partitioning the transition Open at the top for easy retrofitting, even with cables already inserted Cable link extendible upwards by 1 U, by using an additional cable entry panel with brush strip
Material	Jeklena pločevina Krtačni trak: plastika, UL 94-V0
Površinska obdelava	lakirano
Barva	RAL 9005
Obseg dobave	Cable link Krtačni trak
Možnosti namestitve	Za pritrditev med sprednjo in zadnjo 482,6 mm (19") montažno ravnino
Razdalja med nivoji	500 - 750 mm
Enote	1 U
Nosilnost (statična)	150 N
Primerno za	za namestitev neodvisno od ohišja
Opomba	Assembly parts should be ordered separately
Paketi	1 pc(s).

# Features

---

Neto teža	6,8 kg
Bruto teža	7,239 kg
PCF na paket (od zibelke do vrat)	PCF-Wert 18,78 kg Co <sup>2</sup> e
Carinska tarifna številka	73269098
Opis izdelka	19" cable bridge, depth-variable, 500 - 750 mm, RAL 9005

---