


# Rittal – The System.

Faster – better – everywhere.



## VX 8617.820

## Support rail 48 x 26 mm

State: 4.3.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8617.820 - Support rail 48 x 26 mm for VX, VX SE, PC, IW, AX

For heavy installed equipment such as transformers. T-head screw and slots in the support rail accommodate all mounting dimensions.



## Features

|                            |  |
|----------------------------|--|
| Model No.                  | VX 8617.820  |
| Product description        |  |
| Material                   | Sheet steel  |
| Surface finish             | Zinc-plated  |
| Supply includes            | Assembly parts   |
| VX installation options    | In enclosure width 1000 mm, on the inner mounting level and in the base  |
| VX SE installation options | In enclosure width 1000 mm, on the inner mounting level, in conjunction with adaptor rail for VX compatibility and in the base |
| AX installation options    | In enclosure width 1000 mm, in conjunction with the AX interior installation rail and AX base configuration rail               |
| PC installation options    | In enclosure width 1000 mm, on the inner mounting level, in conjunction with adaptor rail for VX compatibility and in the base |
| WI installation options    | In enclosure width 1000 mm, on the inner mounting level, in conjunction with adaptor rail for VX compatibility and in the base |

# Features

---

|                       |  |
|-----------------------|--|
| To fit                | Enclosure type: VX<br>VX SE<br>PC<br>IW<br>AX<br>CX one-piece console<br>Width: = 1,000 mm |
| Packs of              | 2 pc(s).   |
| Net weight            | 4,64 kg  |
| Gross weight          | 4,913 kg   |
| Customs tariff number | 73269098   |
| ETIM 9                | EC001285   |
| ECLASS 8.0            | 27189261   |
| Product description   | VX Support rail 48 x 26 mm, for W: 1000 mm   |

---