
Rittal - The System.

Faster – better – everywhere.





DK 5502.010 Fan mounting plate

State: 17.11.2025 (Source: rittal.com/si-sl)



DK 5502.010 - Fan mounting plate for VX IT, TS IT, TX CableNet

For active ventilation of the VX IT, TS IT or TE 8000, depending on the version.

Features

DK 5502.010
For active ventilation. The unit may optionally be extended with additional fans.
For use in the cut-out integrated into the roof plate
RAL 7035
1 fan unit
2 fans
1 thermostat
Connection cable, open-ended
Assembly parts
160/180
230 V, 1~, 50 Hz/60 Hz
Width: 200 mm
Height: 59 mm
Depth: 550 mm
1514
In VX IT with W x D (mm): 600 x 600 / 600 x 800 / 600 x 1000 / 600
x 1200 / 800 x 600
In the TS IT with W x D: 600 x 600 / 600 x 800 / 600 x 1000 / 600 x
1200 / 800 x 600
The noise level given refers to the first fan
Connection via distributor box or country-specific connector

© Rittal 2025

Features

To fit	Enclosure type: VX IT TS IT TX CableNet
Operating temperature range	5 °C55 °C
Packs of	1 pc(s).
Net weight	3.027
Gross weight	3.3
Customs tariff number	84149000
EAN	4028177679245
ECLASS 8.0	27189272

Approvals

Declaration of conformity UK

© Rittal 2025 3

Tender text

Fan mounting plate

Fan-mounting plate for active ventilation of an enclosure. For tool-less use in the cut-out integrated into the roof plate of size WxD 120x490 mm. May be used for Rittal enclosure series TS IT. Pre-wired ready for connection with two fans, may be extended to three fans. Including thermostat and connection cable with open end for connection to a distribution box or

Technical specifications for fan Rated operating voltage: 230 V~

Power consumption: 15/14 W at 50/60 Hz

Air throughput (unimpeded air flow): 180/180 m³/h,

country-specific connector by authorized personnel.

50/60 Hz

Noise level (unimpeded air flow): 37 dB (A) Operating temperature range: -10°C to + 55°C

Technical specifications of thermostat Rated operating voltage: 230 V ~ AC Temperature range: +5°C to +55°C

Material: Sheet steel, spray-finished

Colour: RAL 7035

Model No. DK: 5502.010 Manufacturer: Rittal

© Rittal 2025 4