

# Rittal – The System.

Faster – better – everywhere.



## KEL 9301.000 Ex enclosures

State: 6.8.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# KEL 9301.000 - Ex enclosures Stainless steel, empty enclosure with screw fastened cover

Ex enclosure with screw-fastened cover, stainless steel



## Features

Model No.	KEL 9301.000
Design	Ex enclosures
Applications	Zone 1 and 2 or 21 and 22 to 2014/34/EC Ambient temperature range: -30 °C...+80 °C The specified temperatures may be limited by the installed equipment Explosion protection category to EN 60 079: Equipment protection thanks to increased safety (Ex e), equipment protection thanks to enclosure (Ex tb)
Material	Enclosure: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal
Surface finish	Enclosure: Brushed, grain 400, peak-to-valley height < 0.8 µm
Supply includes	Enclosure Cover
Dimensions	Width: 150 mm Height: 150 mm Depth: 80 mm

## Features

Certificate IEC EX PTB 09.0033U	Yes
Certificate PTB 03 ATEX 1013U	Yes
Basic material	Stainless steel 1.4301 (AISI 304)
IP protection category to IEC 60529	IP 66
Packs of	1 pc(s).
Net weight	1.2
Gross weight	1.448
Customs tariff number	94032080
EAN	4028177138544
ETIM 9	EC002503
ECLASS 8.0	27180502

## Approvals

Approvals	ATEX IEC Ex
Explanations	Manufacturer's declaration