

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.050

## Nosilec zbiralnih sponk

State: 30.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.050 - Nosilec zbiralnih sponk za ploščate bakrene zbirane sponke

Za ploščate bakrene vodnike do 800 A.

## Features

Št. Modela	SV 9340.050
Zasnova	UL certifikat
Product modification	Zaradi težav pri dobavi plastičnih dodatkov so trenutno dolgi dobavni roki. Kot protiukrep so bili za izboljšanje dobavne zmogljivosti preizkušeni in certificirani alternativni materiali. Posledično bodo nekateri izdelki v prihodnje dobavljeni v črni barvi (podobno kot RAL 9005). Ta ukrep nima nobenega vpliva na druge tehnične lastnosti, odobritve in certifikate.
Material	Poliamid Protipožarna zaščita v skladu z UL 94-V0
Barva	RAL 7035
Nazivna delovna napetost	1000 V, 3~ 1500 V (DC)
Opomba za model št.	Za UL aplikacije je potrebna uporaba osnovne plošče.
Električne nazivne vrednosti UL (SCCR)	14 kA - 600 V, support spacing 500 mm, 12 x 5/10 mm busbars 22 kA - 600 V, support spacing 500 mm, 15 x 5 - 25 x 10 mm busbars 25 kA - 600 V, support spacing 250 mm, 12 x 5/10 mm busbars 25 kA - 600 V, support spacing 500 mm, 30 x 5/10 mm busbars 30 kA - 600 V, support spacing 250 mm, 15 x 5 - 25 x 10 mm busbars 50 kA - 600 V, support spacing 350 mm, 30 x 5/10 mm busbars, Fuse Class L max. 800 A, JDDZ/7 54 kA - 600 V, support spacing 500 mm, 30 x 5/10 mm busbars, circuit breaker max. 600 A, DIVQ/7 65 kA - 480 V, support spacing 250 mm, 30 x 5/10 mm busbars, circuit breaker max. 600 A, DIVQ/7 73 kA - 600 V, support spacing 250 mm, 30 x 5/10 mm busbars, Fuse Class L max. 800 A, JDDZ/7

# Features

Število polov	3-pole
Za model št.	3580000 3581000 3582000 3583000 3584000 3580100 3581100 3585005 3586005
Notranja namestitev	Yes
Razmak med središči zbiralnih sponk	60 mm
Za namestitev zbiralnih sponk	12 x 5 - 30 x 10
Paketi	4 pc(s).
Neto teža	0,668 kg
Bruto teža	0,72 kg
Carinska tarifna številka	85469010
ETIM 9	EC001166
ECLASS 8.0	27400607
Opis izdelka	SV Busbar support, 3-pole, 60 mm centre-to-centre spacing, for busbar WxH: 12x5-30x10 mm, UL version

# Approvals

Approvals	ABS DNV Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK