

Rittal – The System.

Faster – better – everywhere.



SV 9340.270

OM nosilci

State: 13.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

SV 9340.270 - OM nosilci brez kontaktne sistema

Za namestitev stikalnih naprav z zunanjim napajanjem.

Features

Št. Modela	SV 9340.270
Zasnova	brez kontaktne sistema
Opis izdelka	Za montažo stikalne opreme z zunanjim napajanjem.
Material	Poliamid Protipožarna zaščita v skladu z UL 94-V0
Barva	Ogrodje: RAL 7035
Za sisteme palic z razmakom med središči	60 mm
Vrsta podporne tirnice	Support frame, 1 x TS 55D-V
Število polov	3-pole
Podporni okvir	Yes
Mere	Širina: 55 mm Višina: 272 mm
Podporne tirnice količina/višina	1 / 10 mm
Za namestitev zbiralnih sponk	Višina: 5, 10 mm
Podporni okvir (Š x V)	55 mm x 237 mm
Odobritve	UL
Paketi	1 pc(s).
Neto teža	0,25 kg
Bruto teža	0,258 kg
Carinska tarifna številka	85369095
ETIM 9	EC001166
ECLASS 8.0	27400607

Features

Opis izdelka

SV OM Support, WH: 55x272 mm, support frame, support rail TS 55D-V, without contact system

Approvals

Approvals

ABS
DNV
Lloyds Register
UL + C-UL (listed)

Explanations

Declaration of conformity
Declaration of conformity UK