

Rittal – The System.

Faster – better – everywhere.



SV 9340.270 OM supports

State: 5.8.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.270 - OM supports without contact system

For mounting of switchgear with external power supply.

Features

Model No.	SV 9340.270
Product description	For mounting of switchgear with external power supply.
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
For bar systems with centre-to-centre spacing	60 mm
Number of poles	3-pole
Support frame support	Yes
Dimensions	Width: 55 mm Height: 272 mm
Support rails Qty/height	1 / 10 mm
To fit busbars	Height: 5, 10 mm
Support frame (W x H)	55 mm x 237 mm
Packs of	1 pc(s).
Net weight	0.25
Gross weight	0.258
Customs tariff number	39269097
EAN	4028177502475
ETIM 9	EC001166
ECLASS 8.0	27400607

Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

OM support (without contact system)
OM support without contact system (3-pole)
for busbar thickness 5/10 mm and PLS 800/1600
Technical specifications
Construction width: 55 mm
Length: 272 mm
Support frame: 55 x 237 mm
Support frame support: yes
PinBlock: -
Support rail: 1
System:
Rittal RiLine60