

Rittal – The System.

Faster – better – everywhere.



SV 9340.620 OM adaptors

State: 8.2.2026 (Source: ittal.com/si-sl)



SV 9340.620 - OM adaptors with spring terminals



Features

| | |
|---|--|
| Model No. | SV 9340.620 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Colour | Chassis: RAL 7035 |
| Rated current max. | 65 A |
| Rated operating voltage | 690 V, 3~ |
| For bar systems with centre-to-centre spacing | 60 mm |
| Support rail type | without support frame, 1 x TS 55E, 1 x TS 55D |
| Number of poles | 3-pole |
| Note on Model No. | According to a heat dissipation test to IEC 61 439-1, a current carrying capacity of up to 80 A is supported |
| Dimensions | Width: 55 mm Height: 208 mm |
| Connection of round conductors | 2.5 - 16 mm ² |
| Support rails Qty/height | 2 / 10 mm |
| To fit busbars | Height: 5, 10 mm |
| Packs of | 1 pc(s). |
| Net weight | 0.299 |

Features

| | |
|------------------------------|---------------|
| Gross weight | 0.348 |
| Copper weight (kg per piece) | 0.059 |
| Customs tariff number | 85369095 |
| EAN | 4028177561786 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |

Approvals

| | |
|--------------|---|
| Approvals | ABS DNV-GL Lloyds Register of Shipping |
| Explanations | Declaration of conformity Declaration of conformity UK |

Tender text

OM adaptor 65 A
OM adaptor 65 A with tension spring clamp, 3-pole,
for busbar thickness 5/10 mm and PLS 800/1600

Technical specifications

Construction width: 55 mm
Length: 208 mm
Support frame: -
Support frame support: -
Support rail: 2
System:
Rittal RiLine60