

Rittal – The System.

Faster – better – everywhere.



SV 9340.630 OM adapterji

State: 3.7.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.630 - OM adapterji z vzmetnimi priključki



Features

| | |
|--|---|
| Št. Modela | SV 9340.630 |
| Zasnova | z vzmetnimi priključki |
| Material | Poliamid Protipožarna zaščita v skladu z UL 94-V0 |
| Barva | Ogrodje: RAL 7035 |
| Maks. nazivni tok | 65 A |
| Nazivna delovna napetost | 690 V, 3~ |
| Za sisteme palic z razmakom med središči | 60 mm |
| Vrsta podporne tirnice | Support frame, 1 x TS 55E |
| Število polov | 3-pole |
| Opomba za model št. | V skladu s testom odvajanja toplote po standardu IEC 61 439-1 je podprta tokovna nosilnost do 80 A. |
| Mere | Širina: 55 mm Višina: 208 mm |
| Priklop okroglih vodnikov | 2,5 - 16 mm ² |
| Podporne tirnice količina/višina | 1 / 10 mm |
| Za namestitev zbiralnih sponk | Višina: 5, 10 mm |
| Podporni okvir (Š x V) | 55 mm x 170 mm |

Features

| | |
|---------------------------|---|
| Paketi | 1 pc(s). |
| Neto teža | 0,32 kg |
| Bruto teža | 0,33 kg |
| Teža bakra (kg na kos) | 0,059 |
| Carinska tarifna številka | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Opis izdelka | SV OM adaptor, 65 A, 690 V, 3-pole, tension spring clamp 2,5-16 mm ² , WH: 55x208 mm, support frame, support rail TS 55E |

Approvals

| | |
|--------------|---|
| Approvals | ABS DNV Lloyds Register |
| Explanations | Declaration of conformity Declaration of conformity UK |