

Rittal – The System.

Faster – better – everywhere.



SV 9340.830

Dvojna žica

State: 28.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.830 - Dvojna žica za OM adapterje z vzmetnimi sponkami 2,5–16 mm²

Predsestavljene priključni kabli za individualen priklop do dveh stikalnih enot na adapter.



Features

Št. Modela	SV 9340.830
Opis izdelka	Predsestavljene priključni kabli za individualen priklop največ dveh stikalnih naprav na adapter.
Material	PVC izolacija Temperaturno odporno do 105 °C Konci žic ultrazvočno zatesnjeni na obeh straneh
Opomba	AWG = American Wire Gauge
AWG	AWG 8 = 8.37 mm ² 10 mm ²
Mere	Dolžina: 140 mm, 250 mm
Paketi	6 pc(s).
Neto teža	0,18 kg
Bruto teža	0,248 kg
Teža bakra (kg na kos)	0,02
Carinska tarifna številka	85444290
ETIM 9	EC000839
ECLASS 8.0	27400613
Opis izdelka	SV Twin cord, AWG 8, L1: 140 mm, L2: 250 mm

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK