

Rittal – The System.

Faster – better – everywhere.



SV 9341.050

Nosilec PLS zbiralnih sponk

State: 3.7.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9341.050 - Nosilec PLS zbiralnih sponk

For PLS special busbars 800 A/1600 A, 3-pole and 4-pole, suitable for top-mounting.

Features

Št. Modela	SV 9341.050
Material	Poliamid Protipožarna zaščita v skladu z UL 94-V0
Barva	RAL 7035
Nazivna delovna napetost	1000 V, 3~ 1500 V (DC)
Opomba za model št.	Za UL aplikacije je potrebna uporaba osnovne plošče. UL odobritev velja samo v povezavi z AC aplikacijami
Električne nazivne vrednosti UL (SCCR)	14 kA - 600 V, support spacing 500 mm, PLS 800 busbars 22 kA - 600 V, support spacing 200 mm, PLS 800 busbars 50 kA - 600 V, support spacing 250 mm, PLS 800 busbars, circuit breaker max. 600 A, DIVQ/7 50 kA - 600 V, support spacing 250 mm, PLS 800 busbars, Fuse Class L max. 800 A, JDDZ/7 65 kA - 480 V, support spacing 150 mm, PLS 800 busbars, circuit breaker max. 600 A, DIVQ/7 65 kA - 600 V, support spacing 150 mm, PLS 800 busbars, Fuse Class max. 600 A, JDDZ/7
Zgornja montaža	Yes
Število polov	3-pole
Za namestitev zbiralnih sponk	PLS 800
Za model št.	3516.000 3527.000 3528.000 3528.010 3529.000
Notranja namestitev	Yes

Features

Razmak med središči zbiralnih sponk	60 mm
Odobritve	UL
Paketi	4 pc(s).
Neto teža	0,32 kg
Bruto teža	0,368 kg
Carinska tarifna številka	85469010
ETIM 9	EC001166
ECLASS 8.0	27400607
Opis izdelka	SV Busbar support, PLS 800, 3-pole, 60 mm bar centre distance, UL design

Approvals

Approvals	ABS Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK