


Rittal – The System.

Faster – better – everywhere.



SV 9342.050

Nosilec PLS zbiralnih sponk

State: 30.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9342.050 - Nosilec PLS zbiralnih sponk

For PLS special busbars 800 A/1600 A, 3-pole and 4-pole, suitable for top-mounting.

Features

| | |
|--|---|
| Št. Modela | SV 9342.050 |
| Material | Poliamid Protipožarna zaščita v skladu z UL 94-V0 |
| Barva | RAL 7035 |
| Nazivna delovna napetost | 1000 V, 3~ 1500 V (DC) |
| Opomba za model št. | Za UL aplikacije je potrebna uporaba osnovne plošče. UL odobritev velja samo v povezavi z AC aplikacijami |
| Električne nazivne vrednosti UL (SCCR) | 25 kA - 600 V, support spacing 500 mm, PLS 1600 busbars 30 kA - 600 V, support spacing 250 mm, PLS 1600 busbars 35 kA - 600 V, support spacing 150 mm, PLS 1600 busbars 65 kA - 600 V, support spacing 250 mm, PLS 1600 busbars, Fuse Class L max. 1400 A, JDDZ/7 65 kA - 600 V, support spacing 100 mm, PLS 1600 busbars, Fuse Class L max. 1600 A, JDDZ/7 |
| Zgornja montaža | Yes |
| Število polov | 3-pole |
| Za namestitev zbiralnih sponk | PLS 1600 |
| Za model št. | 3516.000 3527.000 3528.000 3528.010 3529.000 |
| Notranja namestitev | Yes |
| Razmak med središči zbiralnih sponk | 60 mm |
| Odobritve | UL |

Features

| | |
|---------------------------|---|
| Paketi | 4 pc(s). |
| Neto teža | 0,56 kg |
| Bruto teža | 0,601 kg |
| Carinska tarifna številka | 85469010 |
| ETIM 9 | EC001166 |
| ECLASS 8.0 | 27400607 |
| Opis izdelka | SV Busbar support, PLS 1600, 3-pole, 60 mm bar centre distance, UL design |

Approvals

| | |
|--------------|---|
| Approvals | ABS Lloyds Register UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |