

Rittal – The System.

Faster – better – everywhere.



DK 7010.180 Access control

State: 23.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7010.180 - Access control for CMC III, PDU, LCP, IoT interface

Access control

Features

Št. Modela	DK 7010.180
Zasnova	Access control
Prednosti	Hitra povezava in samodejno zaznavanje s funkcijo plug & play Napajanje se omogoči s povezavo z vmesnikom CAN-BUS.
Aplikacije	Nadzor ohišij v IT, industriji in upravljanju objektov Nadzor ohišij, prostorov in zabojnikov v IT okolju
Način delovanja	For connecting two handles and two reader units to monitor doors Vgrajen IR senzor dostopa Built-in vandalism sensor
Material	Plastika
Površinska obdelava	Spredaj: gladko Ohišje: teksturirano
Barva	RAL 9005
Obseg dobave	Senzor Montažna plošča Sestavni deli
Povezava s CAN vodilom	Direct
Vmesniki	2 x RJ45 CAN bus 2 x RJ12 2 x flat-pin connectors Jack
Mere	Širina: 110 mm Višina: 30 mm Globina: 40 mm
Delovno temperaturno območje	0 °C...55 °C

Features

Vlažnost okolice (brez kondenzacije)	5...95 %
Paketi	1 pc(s).
Neto teža	0,166 kg
Bruto teža	0,169 kg
Carinska tarifna številka	85311095
ETIM 9	EC002627
Opis izdelka	DK Access control, connection via CAN bus interface, WxHxD: 110x30x40 mm, RAL 9005

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity