

Rittal – The System.

Faster – better – everywhere.



DK 7030.060 CMC III power pack

State: 6.9.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7030.060 - CMC III power pack for PU, PU Compact, LED light strip, door control module

CMC III power pack for use across multiple voltage ranges.



Features

| | |
|----------------------------|---|
| Model No. | DK 7030.060 |
| Product description | The power pack is specifically tailored to the CMC III design and may be positioned in a mounting unit. As well as a special connector for the CMC III Processing Unit/Compact, there are also two further terminals available as 24 V outputs. |
| Material | Plastic |
| Surface finish | Front: Smooth Enclosure: Textured |
| Colour | Front: RAL 9005 Enclosure: RAL 7035 |
| Supply includes | Connection cable 24 V (DC) Assembly parts for mounting on surfaces |
| Length of connection cable | 600 mm |
| Input connection | IEC 320 connector C14 |
| Output current (max.) | 2,5 A |

Features

| | |
|-----------------------------------|---|
| Dimensions | Width: 138 mm Height: 40 mm Depth: 132 mm |
| Operating temperature range | 0 °C...40 °C |
| Output voltage | Output voltage: 24 V DC |
| Ambient humidity (non-condensing) | 5...95 % |
| Packs of | 1 pc(s). |
| Net weight | 0.65 |
| Gross weight | 0.652 |
| Customs tariff number | 85043121 |
| EAN | 4028177659384 |
| ETIM 9 | EC002627 |
| ECLASS 8.0 | 27189253 |

Approvals

| | |
|--------------|---|
| Approvals | UL |
| Explanations | Manufacturer's declaration Declaration of conformity |

Tender text

7030.060

CMC III power pack

Packs of 1

Compact plastic housing with ventilated front in RAL 9005.

Housing in RAL 7035, Integrated green LED as status display.

The CMC III power pack is used to supply the Processing Unit with power.

It can either be connected to the jack or the terminal of the redundant energy inputs. In addition, the connection can be used for additional power supply to the CMC III CAN bus unit.

Technical specifications:

Input: C14 100-230 V, 50/60 Hz

Output: 24 V DC, 2 A

WxHxD: 138 x 40 x 120+12 Front mm

Temperature application range:

0 °C to 40° C

Humidity range:

5% to 95% relative humidity, non-condensing

Protection category: IP 30 to IEC 60 529

Included in the pack: Unit, quick reference guide, side mounting and top-hat rail mounting set