


Rittal – The System.

Faster – better – everywhere.



SV 9344.040 NH ločilnik

State: 14.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9344.040 - NH ločilnik z elektromehanskim nadzorom varovalk

Features

Št. Modela	SV 9344.040
Zasnova	Za namestitev montažne plošče
Material	Poliamid Protipožarna zaščita v skladu z UL 94 Kontakti: elektrolitski baker s srebrno prevleko
Barva	Ogrodje: RAL 7035 Pokrov: RAL 7035/7001
Vpenjalna površina za laminirane bakrene palice	Širina vpenjalnega območja: 13 mm Višina vpenjalnega območja: 13 mm
for mounting plate assembly	Yes
Kabelska vtičnica	Top/bottom
Vrsta električne povezave	Box terminal
Nazivni obratovalni tok maks.	160 A
Nazivna delovna napetost	690 V, 3~
Za velikost NH	00
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (talilne varovalke)
Mere	Širina: 106 mm Višina: 194 mm
Priklop okroglih vodnikov	4 - 95 mm ²
Število polov	3-pole
Round conductor cross-section	4 - 95 mm ²
Paketi	1 pc(s).
Neto teža	1,17 kg

Features

Bruto teža	1,172 kg
Teža bakra (kg na kos)	0,15
Carinska tarifna številka	85369095
ETIM 9	EC000249
ECLASS 8.0	27371401
Opis izdelka	SV NH fuse-switch disconnecter, size 00, 160 A, 690 V, 3-pole, box terminal, with electromechanical fuse monitoring, for mounting plate assembly

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK