

Rittal – The System.

Faster – better – everywhere.



RX 9360.200

RiLineX connection adaptor

State: 22.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.200 - RiLineX connection adaptor

RiLineX connection adaptor for 60 mm busbar systems. The adaptor boasts an impressive compact design and simple conductor connection. Dismantling requires the use of tools. Round conductors may be connected either from above or below. The push-in connection clamps are designed for easier connection. Mounted by simply snapping onto the RiLineX board. The connection adaptor features a high current-carrying capacity plus high levels of short-circuit protection and universal contact hazard protection that adapts to the relevant wire gauge. The device features semi-automatic adjustment of the busbar thickness between 5 and 10 mm.



Features

Št. Modela	RX 9360.200
Prednosti	Mounting on the busbar system and cable connection with just one screw
Material	Poliamid (PA 6) Protipožarna zaščita v skladu z UL 94
Barva	RAL 9005
Nazivni tok (maks.)	67 A
Maks. nazivni tok	76 A
Rated current of round conductor	76 A
Rated current of round conductor (UL)	66 A

Features

Električne nazivne vrednosti UL (SCCR)	5 kA - 600 V, RMS 35 kA - 480 V, circuit breaker max. 60 A, DIVQ/7 100 kA - 600 V, Fuse Class J max. 100 A, JDDZ/7
Kabelska vtičnica	Top/bottom
Za sisteme palic z razmakom med središči	60 mm
Število polov	3-pole
Za namestitev sistema zbiralnih sponk	RiLineX RiLine60
Mere	Širina: 26,8 mm Višina: 239,2 mm Globina: 103,3 mm
Priklop okroglih vodnikov	1,5 - 16 mm ²
Za namestitev zbiralnih sponk	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	800 V AC 800 V DC 600 V AC (UL) 600 V DC (UL)
Kategorija prenapetosti	4
Stopnja kontaminacije	3
Standardi	IEC/EN 61439-1 UL 508
Nazivna impulzna vzdržna napetost U _{imp}	8 kV
Rated insulation voltage U _i	800 V
Izguba toplote maks.	7 W
IP razred zaščite po IEC 60 529	IP 2XB
Maximum operating air humidity	90 %
Delovno temperaturno območje	-5 °C...55 °C

Features

Temperaturno območje shranjevanja	-25 °C...75 °C
Vlažnost okolice (brez kondenzacije)	10...90 %
Za debelino palice	1,5 - 16 mm
Paketi	4 pc(s).
Neto teža	1,2 kg
Bruto teža	1,656 kg
PCF na paket (od zibelke do vrat)	13,4
Carinska tarifna številka	85369010
ETIM 9	EC001531
Opis izdelka	RiLineX connection adaptor for 60 mm busbar systems. The adaptor boasts an impressive compact design and simple conductor connection. Dismantling requires the use of tools. Round conductors may be connected either from above or below. The push-in connection clamps are designed for easier connection. Mounted by simply snapping onto the RiLineX board. The connection adaptor features a high current-carrying capacity plus high levels of short-circuit protection and universal contact hazard protection that adapts to the relevant wire gauge. The device features semi-automatic adjustment of the busbar thickness between 5 and 10 mm.

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration