

# Rittal – The System.

Faster – better – everywhere.



## RX 9360.230

## RiLineX connection adaptor

State: 25.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.230 - RiLineX connection adaptor

RiLineX connection adaptor for 60 mm busbar systems. The adaptor boasts an impressive compact design and simple conductor connection. Dismantling requires the use of tools. Conductors may be connected either from above or below. The connection clamps support through-wiring. Mounted by simply snapping onto the RiLineX board. The supply leads and adaptors are screw-fastened onto the board together. The connection adaptor features a high current-carrying capacity plus high levels of short-circuit protection and universal contact hazard protection that adapts to the relevant wire gauge. The device has a screw fastening, and is suitable for bar widths of between 5 and 10 mm.



## Features

Št. Modela	RX 9360.230
Prednosti	Mounting on the busbar system and cable connection with just one screw
Material	Poliamid (PA 6) Protipožarna zaščita v skladu z UL 94
Barva	RAL 9005
Nazivni tok (maks.)	375 A
Maks. nazivni tok	630 A
Rated current of round conductor	630 A
Rated current of round conductor (UL)	600 A

# Features

Rated current of laminated copper bar	790 A
Rated current of laminated copper bar (UL)	760 A
Električne nazivne vrednosti UL (SCCR)	27,5 kA - 600 V, RMS, unprotected 100 kA - 600 V, circuit breaker max. 400 A, DIVQ/7 100 kA - 600 V, Fuse Class L max. 1200 A, JDDZ/7
Kabelska vtičnica	Top/bottom
Za sisteme palic z razmakom med središči	60 mm
Število polov	3-pole
Za namestitev sistema zbiralnih sponk	RiLineX RiLine60
Mere	Širina: 126,8 mm Višina: 239,4 mm Globina: 104,6 mm
Priklop okroglih vodnikov	95 - 240 mm <sup>2</sup>
Vpenjalna površina za laminirane bakrene palice (Š x V)	24 x 20 mm
Rated voltage	1.000 V AC 1.500 V DC 600 V AC (UL) 600 V DC (UL)
Kategorija prenapetosti	4
Stopnja kontaminacije	3
Standardi	IEC/EN 61439-1 UL 508
Nazivna impulzna vzdržna napetost U <sub>imp</sub>	12 kV
Rated insulation voltage U <sub>i</sub>	1.000 V
Izguba toplote maks.	20 W
IP razred zaščite po IEC 60 529	IP 2XB

# Features

Maximum operating air humidity	90 %
Delovno temperaturno območje	-5 °C...55 °C
Temperaturno območje shranjevanja	-25 °C...75 °C
Vlažnost okolice (brez kondenzacije)	10...90 %
Paketi	1 pc(s).
Neto teža	1,5 kg
Bruto teža	1,62 kg
PCF na paket (od zibelke do vrat)	8,65
Carinska tarifna številka	85369010
ETIM 9	EC001531
Opis izdelka	RiLineX connection adaptor for 60 mm busbar systems. The adaptor boasts an impressive compact design and simple conductor connection. Dismantling requires the use of tools. Conductors may be connected either from above or below. The connection clamps support through-wiring. Mounted by simply snapping onto the RiLineX board. The supply leads and adaptors are screw-fastened onto the board together. The connection adaptor features a high current-carrying capacity plus high levels of short-circuit protection and universal contact hazard protection that adapts to the relevant wire gauge. The device has a screw fastening, and is suitable for bar widths of between 5 and 10 mm.

# Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration