

Rittal – The System.

Faster – better – everywhere.



DK 7641.000 Stenska AE ohišja

State: 21.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7641.000 - Stenska AE ohišja z montažnimi kotniki 482,6 mm (19"), spremenljiva globina

Wall-mounted enclosure for small networks with fixed 482.6 mm (19") mounting level and gland plate with brush strip for cable entry at the bottom. Protection category IP 55.

Features

Št. Modela	DK 7641.000
Material	Ohišje: jeklena pločevina
Površinska obdelava	Ohišje: prašno barvano Montažni kotni nosilci: pocinkano
Barva	RAL 7035
Obseg dobave	Ohišje z vrati na tečajih Vrata s tečaji na desni, možnost menjave na levo Ključavnica z dvojnimi 3 mm vložkom Plošča z uvodnicami s krtačnim trakom za vhod kablov v dno ohišja Montažni kotniki, 482,6 mm (19"), popolnoma nastavljivi po globini C profil za vpenjanje kablov na zadnji plošči Kovinski nosilec za opcijsko namestitev ozemljitvene tirnice ali 482,6 mm (19") vtičnic
Enote	8 U
Mere	Širina: 600 mm Višina: 380 mm Globina: 350 mm
Globina namestitve	310 mm
Višina vgradnje komponent	8 U
Položaj tečajev vrat	right, may be swapped to the left
Število ključavnic	1
Osnovni material	Sheet steel
Razred zaščite po IEC 60 529	Up to IP 66 (depending on the selected gland pate)

Features

Plošča za kableske uvodnice	Velikost: 5 Količina: 1
Paketi	1 pc(s).
Neto teža	17,23 kg
Bruto teža	18,137 kg
Carinska tarifna številka	94032080
ECLASS 8.0	27180208
Opis izdelka	DK Wall-mounted enclosures AE, WHD:600x380x350 mm, 8 U, AE 1339

Approvals

Approvals	TÜV VDE
-----------	------------