

Rittal – The System.

Faster – better – everywhere.



DK 7643.000

Stenska AE ohišja

State: 15.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7643.000 - Stenska AE ohišja z montažnimi kotniki 482,6 mm (19"), spremenljiva globina

Wall-mounted enclosure for small networks with fixed 482.6 mm (19") mounting level and gland plate with brush strip for cable entry at the bottom. Protection category IP 55.

Features

Št. Modela	DK 7643.000
Material	Ohišje: jeklena pločevina
Površinska obdelava	Ohišje: prašno barvano Montažni kotni nosilci: pocinkano
Barva	RAL 7035
Obseg dobave	Ohišje z vrati na tečajih Vrata s tečaji na desni, možnost menjave na levo Ključavnica z dvojnimi 3 mm vložkom Plošča z uvodnicami s krtačnim trakom za vhod kablov v dno ohišja Montažni kotniki, 482,6 mm (19"), popolnoma nastavljivi po globini C profil za vpenjanje kablov na zadnji plošči Kovinski nosilec za opcijsko namestitev ozemljitvene tirnice ali 482,6 mm (19") vtičnic
Enote	13 U
Mere	Širina: 600 mm Višina: 600 mm Globina: 350 mm
Globina namestitve	310 mm
Višina vgradnje komponent	13 U
Položaj tečajev vrat	right, may be swapped to the left
Število ključavnic	2
Osnovni material	Sheet steel
Razred zaščite po IEC 60 529	Up to IP 66 (depending on the selected gland pate)

Features

Plošča za kableske uvodnice	Velikost: 5 Količina: 1
Paketi	1 pc(s).
Neto teža	23,399 kg
Bruto teža	25 kg
Carinska tarifna številka	94032080
ECLASS 8.0	27180208
Opis izdelka	DK Wall-mounted enclosures AE, WHD:600x600x350 mm, 13 U, AE 1360

Approvals

Approvals	TÜV VDE
-----------	------------