

Rittal – The System.

Faster – better – everywhere.



RX 9360.635

RiLineX CB component adaptor

State: 1.9.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.635 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 630 A) for 60 mm busbar systems. The device width is 140 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. The cable outlet is easily converted to the top or bottom to suit individual requirements.



Features

Model No.	RX 9360.635
Design	universal
Benefits	Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure
Material	Polyamide (PA 6) Fire protection corresponding to UL 94
Colour	RAL 9005 RAL 35745
Supply includes	Including 3 connection space covers, 2 cross members and assembly parts
IP protection category to IEC 60529	IP 2XB
Rated current max.	630 A
Rated current (UL)	500 A

Features

Rated impulse withstand voltage U _{imp}	12 kV
Rated voltage	690 V AC 690 V DC 600 V AC (UL)
Rated insulation voltage	1.000 V
Overvoltage category	4
Contamination level	3
Number of poles	3-pole
Cable outlet	Top/bottom
Type of electrical connection	Screw M10
To fit busbar system	RiLineX RiLine60
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Operating temperature range	-25 °C...55 °C
Storage temperature range	-25 °C...75 °C
Dimensions	Width: 140 mm Height: 325 mm
Packs of	1 pc(s).
Net weight	4.52
Gross weight	4.722
Copper weight (kg per piece)	2.64
Customs tariff number	85369095
EAN	4028177997066
ETIM 9	EC001531

Approvals

Approvals

UL + C-UL (listed)