


# Rittal – The System.

Faster – better – everywhere.



## RX 9360.710

### RiLineX component adaptor

State: 6.2.2026 (Source: [ittal.com/si-sl](http://ittal.com/si-sl))

# RX 9360.710 - RiLineX component adaptor

RiLineX component adaptor (16 A, 3-pole, including connection cables) in width 45 mm for RiLineX and other 60 mm busbar system platforms. With fitted support rail for snap-on mounting of equipment and tool-free adjustment.



## Features

|                                       |   |
|---------------------------------------|---|
| Model No.                             | RX 9360.710   |
| Design                                | With connection cable   |
| Benefits                              | <p>For mounting equipment for top hat rail installation, e.g. motor starter</p> <p>Pre-assembled connection cable</p> <p>Simple clip locking for support rails</p> <p>Optional anti-slip guard</p> <p>Snap-on mounting and simple adjustment for busbar thickness (5/10 mm)</p> <p>Simple assembly</p> <p>Coordinated accessories reduce the number of different items required</p> |
| Material                              | <p>Polyamide (PA 6)</p> <p>Fire protection corresponding to UL 94</p>   |
| Colour                                | <p>RAL 9005</p> <p>RAL 35745</p>  |
| Connection cables (AWG)               | AWG 14  |
| Rated current of round conductor      | 16 A  |
| Rated current of round conductor (UL) | 16 A  |

# Features

|   |   |
|---|---|
| Electrical ratings UL (SCCR)                  | 5 kA - 600 V, RMS, unprotected<br>100 kA - 600 V, Fuse Class RK5 max. 30 A, JDDZ/7<br>65 kA - 480 V, Combination Motor Controller max. 16 A, NKJH/7<br>30 kA - 600 V, Combination Motor Controller max. 12.5 A, NKJH/7<br>65 kA - 480 V, Combination Motor Controller max. 40 A, NKJH/7<br>50 kA - 480 V, circuit breaker max. 22 A, DIVQ/7 |
| Cable outlet                                  | Top   |
| For bar systems with centre-to-centre spacing | 60 mm   |
| Length of connection cable                    | 150 mm  |
| Number of poles                               | 3-pole  |
| To fit busbar system                          | RiLineX<br>RiLine60   |
| Dimensions                                    | Width: 45 mm<br>Height: 239.4 mm<br>Depth: 36.2 mm  |
| Support rails Qty/height                      | 1 / 10 mm   |
| To fit busbars                                | 15 x 5/10<br>20 x 5/10<br>30 x 5/10   |
| Rated voltage                                 | 690 V AC<br>600 V AC (UL)<br>600 V DC (UL)  |
| Overvoltage category                          | 4   |
| Contamination level                           | 3   |
| Standards                                     | IEC 61 439-1/-2<br>UL 508   |
| IP protection category to IEC 60 529          | IP 2XB  |
| Operation humidity max                        | 90 %  |
| Operating temperature range                   | -5 °C...55 °C   |
| Storage temperature range                     | -25 °C...75 °C  |

## Features

---

|                                   |               |
|-----------------------------------|---------------|
| Ambient humidity (non-condensing) | 10...90 %     |
| Packs of                          | 4 pc(s).      |
| Net weight                        | 1.2           |
| Gross weight                      | 1.35          |
| Copper weight (kg per piece)      | 0.108         |
| Customs tariff number             | 85369095      |
| EAN                               | 4028177997035 |
| ETIM 9                            | EC001531      |

---

## Approvals

---

|              |                           |
|--------------|---------------------------|
| Approvals    | UL + C-UL (listed)        |
| Explanations | Declaration of conformity |

---