## Rittal – The System.

Faster - better - everywhere.





# DK 7856.230 PSM socket modules

State: 15.12.2025 (Source: rittal.com/si-sl)



## DK 7856.230 - PSM socket modules

The various modules may be inserted into the support rail in any combination.

### **Features**

Model No.	DK 7856.230
Design	non-switchable
Product description	The modular system facilitates basic configuration of the racks, thanks to a vertical support rail with single-/3-phase infeed. The various socket modules to supply the active components may be snap-fitted into the support rail. The various modules, earthing pins, IEC320 etc. may be inserted into the support rail in any combination. This is easily achieved, even by non-electricians, thanks to the shock hazard protected plug & play system.
Material	Section: Aluminium, anodised Socket inserts: Plastic (PA6 GF 30 V1)
Length	250 mm
Type of electrical connection	WAGO WINSTA MIDI
Phases per infeed	1~
Thermal overcurrent protection	-
Rated operating voltage	110 V - 230 V AC, 50/60 Hz
Rated current (max.)	16 A
Required number of module slots	1
Dimensions	Length: 250 mm
Operating temperature range	5 °C45 °C
Ambient humidity (non-condensing)	595 %
Sockets	4 x IEC 320 socket C19
Packs of	1 pc(s).
Net weight	0.3

© Rittal 2025

#### **Features**

Gross weight	0.341
Customs tariff number	85369001
EAN	4028177485358
ETIM 9	EC000330
ECLASS 8.0	27142604

## **Approvals**

Approvals	IEC CB UR + C-UR (recognized)
	VDE
	Declaration of conformity

### Tender text

PSM plug-in module IEC 320 C19
The plug-in module for the busbar system PSM has 4 current outlets with IEC320 C19 slots.
A PSM busbar is required to operate the module.
A maximum of 4 modules may be inserted into a 1200 mm long PSM bar, and a maximum of 7 modules into a 2000 mm long PSM bar.

© Rittal 2025