


# Rittal – The System.

Faster – better – everywhere.



## TE 7888.460

## Omrežni nosilec TE 8000

State: 21.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TE 7888.460 - Omrežni nosilec TE 8000

TE 8000 IT enclosure with glazed door, prepared for individual interior installation.

## Features

|                     |  |
|---------------------|--|
| Št. Modela          | TE 7888.460  |
| Zasnova             | s stranskimi ploščami  |
| Prednosti           | Brez okvirja<br>Optimalna dostopnost<br>Enostavno razstavljanje in tudi enostavna namestitvev<br>Zamenljiv tečaj vrat  |
| Material            | Jeklena pločevina<br>Steklena vrata: enoslojno varnostno steklo, 3 mm  |
| Površinska obdelava | Montažni okvir: Temeljni premaz<br>Plošče ohišja: prašno barvano   |
| General colour      | RAL 7035   |
| Barva               | RAL 7035   |
| Obseg dobave        | Samostoječi 482,6 mm (19") montažni okvirji, spredaj in zadaj, z nastavljivo globino<br>Steklena sprednja vrata, vključno s 130° tečajem, okrasnim ročajem in varnostno ključavnico 3524 E<br>Vrata iz jeklene pločevine na zadnji strani, vključno s 130° tečajem, varnostna ključavnica 3524 E<br>Osnovni okvir z največjim izrezom (za opsijsko postavitvev z modularnimi ploščami)<br>Strešna plošča s skritim izrezom za vhod kablov in opsijskim ventilatorjem<br>4 nivelirne noge, M10 (priložene)<br>4 distančniki, 20 mm (priloženi) za dvig strešne plošče<br>Stranske plošče, možnost zaklepanja, vključno z varnostno ključavnico 3524 E |
| Mere                | Širina: 800 mm<br>Višina: 1.200 mm<br>Globina: 800 mm  |

# Features

|   |  |
|---|--|
| Enote   | 24 U   |
| Enote   | 24 U   |
| Prosti montažni prostor do višine 482,6 mm (19"), spredaj/zadaj | 130 mm / 130 mm /  |
| Razdalja med nivoji (kot je dobavljeno)                         | 495 mm   |
| Nosilnost   | 4.000 N  |
| Razred zaščite po IEC 60 529                                    | IP 20  |
| Osnovni material  | Sheet steel  |
| Paketi  | 1 pc(s).   |
| Neto teža   | 71,5 kg  |
| Bruto teža  | 74 kg  |
| Carinska tarifna številka                                       | 94032080   |
| ETIM 9  | EC002499   |
| ECLASS 8.0  | 27180207   |
| Opis izdelka  | TE Network enclosure TE 8000, WHD: 800x1200x800 mm, 24 U, With glazed door |

# Approvals

Explanations

Declaration of conformity