


Rittal – The System.

Faster – better – everywhere.



RX 9360.798

RiLineX component adaptor

State: 10.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.798 - RiLineX component adaptor

RiLineX component adaptor (80 A, 3-pole, including connection cables) in width 72 mm for RiLineX and other 60 mm busbar systems. With integral threaded inserts.



Features

Št. Modela	RX 9360.798
Zasnova	S priključnim kablom
Prednosti	For mounting equipment for top hat rail installation, e.g. motor starter Pre-assembled connection cable Simple clip locking for support rails Optional anti-slip guard Snap-on mounting and simple adjustment for busbar thickness (5/10 mm) Enostavna montaža Coordinated accessories reduce the number of different items required
Material	Poliamid (PA 6) Protipožarna zaščita v skladu z UL 94
Barva	RAL 9005 RAL 35745
Priključni kabli (AWG)	AWG 4
Nazivni tok (maks.)	80 A
Rated current of round conductor	80 A

Features

Rated current of round conductor (UL)	80 A
Električne nazivne vrednosti UL (SCCR)	100 kA - 600 V, Fuse Class J max. 200 A, JDDZ/7 65 kA - 480 V, circuit breaker max. 70 A, DIVQ/7 50 kA - 480 V, Combination Motor Controller max. 100 A, NKJH/7 30 kA - 600 V, Combination Motor Controller max. 75 A, NKJH/7
Kabelska vtičnica	Bottom
Za sisteme palic z razmakom med središči	60 mm
Število polov	3-pole
Za namestitev sistema zbiralnih sponk	RiLineX RiLine60
Mere	Širina: 72 mm Višina: 239,4 mm Globina: 36,6 mm
Za namestitev zbiralnih sponk	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	690 V AC 600 V AC (UL) 600 V DC (UL)
Stopnja kontaminacije	3
Standardi	IEC 61 439-1/-2 UL 508
Nazivna impulzna vzdržna napetost Uimp	8 kV
Rated insulation voltage Ui	1.000 V
IP razred zaščite po IEC 60 529	IP 2XB
Maximum operating air humidity	90 %
Delovno temperaturno območje	-5 °C...55 °C
Temperaturno območje shranjevanja	-25 °C...75 °C

Features

Vlažnost okolice (brez kondenzacije)	10...90 %
Paketi	1 pc(s).
Neto teža	0,7 kg
Bruto teža	0,702 kg
Teža bakra (kg na kos)	0,246
PCF na paket (od zibelke do vrat)	3,9
Carinska tarifna številka	85369095
ETIM 9	EC001531
Opis izdelka	RiLineX component adaptor (80 A, 3-pole, including connection cables) in width 72 mm for RiLineX and other 60 mm busbar systems. With integral threaded inserts.

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration