

Rittal – The System.

Faster – better – everywhere.



RX 9362.350

RiLineX NH fuse-switch disconnecter

State: 22.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9362.350 - RiLineX NH fuse-switch disconnecter

RiLineX NH fuse-switch disconnecter in size 3 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Box terminal connection to connect round conductors ranging from min. 120 to max. 300 mm². Cable outlet can be at the top or bottom, as required.



Features

Št. Modela	RX 9362.350
Zasnova	For 60 mm busbar systems
Prednosti	Cover: can be locked and prepared for a lead seal Voltage test through separate opening Tool-free changeover of the cable outlet Park position for simpler maintenance work All variants also available with electronic fuse monitoring
Material	Poliamid (PA 6) Protipožarna zaščita v skladu z UL 94 Kontakti: elektrolitski baker s srebrno prevleko
Barva	RAL 9005 RAL 35745
Za sisteme palic z razmakom med središči	60 mm
Kabelska vtičnica	Top/bottom
Vrsta električne povezave	Box terminal
Vložki varovalk	NH 3
Nazivna delovna napetost	690 V AC

Features

Za velikost NH	3
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (talilne varovalke)
Mere	Širina: 250 mm Višina: 298,4 mm Globina: 134,9 mm
Delovno temperaturno območje	-5 °C...35 °C
Temperaturno območje shranjevanja	-25 °C...70 °C
Za namestitev zbiralnih sponk	15 x 5/10 20 x 5/10 30 x 5/10
Za namestitev sistema zbiralnih sponk	RiLineX RiLine60
Število polov	3-pole
Stopnja kontaminacije	3
IP razred zaščite po IEC 60 529	IP 2XB
Fire load	52,86 MJ/m ²
Izguba toplote maks.	101 W
Paketi	1 pc(s).
Neto teža	4,7 kg
Bruto teža	4,9 kg
Teža bakra (kg na kos)	2,255
PCF na paket (od zibelke do vrat)	32,06
Carinska tarifna številka	85369095
ETIM 9	EC001040

Features

Opis izdelka

RiLineX NH fuse-switch disconnecter in size 3 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnectors have a park position to make maintenance easier. Box terminal connection to connect round conductors ranging from min. 120 to max. 300 mm². Cable outlet can be at the top or bottom, as required.

Approvals

Approvals

CQC-CCC

Explanations

Declaration of conformity
PCF-declaration