

Rittal – The System.

Faster – better – everywhere.



SV 9393.554

Tokovni transformator

State: 10.7.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9393.554 - Tokovni transformator

Features

| | |
|--------------------------------------|---|
| Št. Modela | SV 9393.554 |
| Zasnova | Izhodna napetost 333 mV |
| Material | Poliamid Protipožarna zaščita v skladu z UL 94 |
| Barva | RAL 9005 |
| Obseg dobave | 2 priključni nogi 2 izolacijski kapi 1 glavna objemka za palico 2 navojna vijaka |
| Za namestitev zbiralnih sponk | 40 x 12 2 x 30 x 10 |
| Primary current | 400 A |
| Standardi | EN 61869-1/2 EN 42600 VDE 0100 EN 50274 / VDE 0660-514 Predpis DGUV 3 |
| Mere | Širina: 60 mm Višina: 80 mm Globina: 30 mm |
| Delovno temperaturno območje | -5 °C...55 °C |
| Temperaturno območje shranjevanja | -25 °C...75 °C |
| Vlažnost okolice (brez kondenzacije) | 10...90 % |
| Osnovna frekvenca | 50...60 Hz |
| Accuracy Class | 0,5 |
| Insulation material (class) | F |

Features

| | |
|---------------------------|-------------------------------------|
| Paketi | 1 pc(s). |
| Neto teža | 0,185 kg |
| Bruto teža | 0,194 kg |
| Carinska tarifna številka | 85043129 |
| ETIM 9 | EC002048 |
| Opis izdelka | SV Current transformer 400 A, 33 mm |

Approvals

| | |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|
