

# Rittal – The System.

Faster – better – everywhere.



## SV 9393.563

# Tokovni transformator

State: 7.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9393.563 - Tokovni transformator

## Features

|                                      |   |
|--------------------------------------|---|
| Št. Modela                           | SV 9393.563   |
| Zasnova                              | Izhodna napetost 333 mV   |
| Material                             | Poliamid<br>Protipožarna zaščita v skladu z UL 94   |
| Barva                                | RAL 9005  |
| Obseg dobave                         | 2 priključni nogi<br>2 izolacijski kapi<br>1 glavna objemka za palico<br>2 navojna vijaka |
| Za namestitev zbiralnih sponk        | 60 x 15<br>2 x 50 x 10  |
| Primary current                      | 1.000 A   |
| Standardi                            | EN 61869-1/2<br>EN 42600<br>VDE 0100<br>EN 50274 / VDE 0660-514<br>Predpis DGUV 3         |
| Mere                                 | Širina: 85 mm<br>Višina: 108 mm<br>Globina: 30 mm   |
| Delovno temperaturno območje         | -5 °C...55 °C   |
| Temperaturno območje shranjevanja    | -25 °C...75 °C  |
| Vlažnost okolice (brez kondenzacije) | 10...90 %   |
| Osnovna frekvenca                    | 50...60 Hz  |
| Accuracy Class                       | 0,5   |
| Insulation material (class)          | F   |

# Features

---

|                           |                                      |
|---------------------------|--------------------------------------|
| Paketi                    | 1 pc(s).                             |
| Neto teža                 | 0,27 kg                              |
| Bruto teža                | 0,284 kg                             |
| Carinska tarifna številka | 85043129                             |
| ETIM 9                    | EC002048                             |
| Opis izdelka              | SV Current transformer 1000 A, 52 mm |

---

# Approvals

---

|              |                           |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|

---