

Rittal – The System.

Faster – better – everywhere.



SV 9677.265 NH tanki ločilniki

State: 12.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.265 - NH tanki ločilniki

3-polni, za sisteme zbiralnih sponk z medosnim razmikom 185 mm.

Features

Št. Modela	SV 9677.265
Zasnova	3-polni, preklopni
Način delovanja	Samodejni hitri kontakt omogoča preklapljanje, neodvisno od uporabnika Dvojni odklop za zanesljiv odklop kontaktov
Material	Poliamid Protipožarna zaščita v skladu z UL 94-V0 Kontaktne tirnice: delno posrebren trd baker
Barva	Ogrodje: RAL 7035 Pokrov: RAL 7001 Ročaj: RAL 7016
Za velikost NH	2
Za sisteme palic z razmakom med središči	185 mm
Kabelska vtičnica	Top
Vrsta električne povezave	Screw M12
Installation type	Screw attachment
Število polov	3-pole
Nazivna delovna napetost	690 V (AC), 3~
Nazivni obratovalni tok maks.	400 A
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (talilne varovalke)
Mere	Širina: 100 mm Višina: 772 mm
Priklop okroglih vodnikov	6 - 240 mm ²
Za namestitev zbiralnih sponk	Višina: 10 mm

Features

Paketi	1 pc(s).
Neto teža	13,5 kg
Bruto teža	14 kg
Teža bakra (kg na kos)	4,003
Carinska tarifna številka	85043129
ETIM 9	EC001040
ECLASS 8.0	27371401
Opis izdelka	SV NH slimline switch disconnecter, size 2, 400 A, 690 V, 3-pole, bolt M12, 185 mm, cable outlet top, screw attachment

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---