

Rittal – The System.

Faster – better – everywhere.



SV 9677.865

Tokovni transformator

State: 21.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.865 - Tokovni transformator

Za induktivno merjenje pretoka toka.

Features

Št. Modela	SV 9677.865
Opis izdelka	Kompaktna zasnova brez spreminjanja globine vgradnje zaradi mehanske integracije v komponente (medosna razdalja 185 mm) omogoča zasnovo, ki prihrani prostor.
Material	Poliamid
Za velikost	1 - 3
Za model št.	9677.100 9677.110 9677.115 9677.200 9677.210 9677.215 9677.300 9677.310 9677.315 9677.340 9677.770 9677.780 9677.900
Nazivna vhodna moč	2,5 VA
Vrsta električne povezave	Box terminal
Insulation material (class)	H
Primary current	250 A
Secondary current	5 A
Accuracy Class	1

Features

Test specification	IEC 60 044-1 EN 60715 DIN VDE 0414 DIN 42 600-2
Priklop okroglih vodnikov	2,5 - 4 mm ²
Nazivna frekvenca	50 - 60 Hz
Paketi	1 pc(s).
Neto teža	0,13 kg
Bruto teža	0,16 kg
Carinska tarifna številka	85044087
ETIM 9	EC002048
ECLASS 8.0	27141146
Opis izdelka	SV current transformer 250 A/5 A for NH slimline fuse-switch disconnecter size 1-3 (SV 9677.XXX)