


Rittal – The System.

Faster – better – everywhere.



VX 9680.608

Sistem povezovalnih ohišij VX25

State: 9.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 9680.608 - Sistem povezovalnih ohišij VX25

Modularno ohišje

VX povezovalni sistemi, za namestitev z delnimi vrati in notranjimi pregradami v modularni izvedbi.

Features

| | |
|-----------------------------------|---|
| Št. Modela | VX 9680.608 |
| Material | Jeklena pločevina, 1,5 mm |
| Površinska obdelava | Okvir ohišja: temeljni premaz Zadnja plošča: temeljni premaz, prašno barvna zunanost, teksturirana barva Plošče z uvodnicami: pocinkano |
| Barva | RAL 7035 |
| Obseg dobave | Okvir ohišja Zadnja plošča Kabelske uvodnice |
| Razred zaščite po IEC 60 529 | Up to IP 54, depending on the panels |
| Test specification | IEC 61 439-1/-2 IEC 61 641 |
| Mere | Širina: 600 mm Višina: 2.000 mm Globina: 800 mm |
| Paketi | 1 pc(s). |
| Neto teža | 44,7 kg |
| Bruto teža | 49,2 kg |
| PCF na paket (od zibelke do vrat) | 132,3 kg CO2 eq (Cat B) |
| Opomba o kategoriji PCF | Kategorija B: PCF vrednost (od zibelke do vrat) na podlagi teže izdelka, približno izračunana in samodeklarirana |
| Carinska tarifna številka | 94032080 |
| ETIM 9 | EC000261 |

Features

| | |
|------------|----------|
| ECLASS 8.0 | 27180101 |
|------------|----------|

| | |
|--------------|--|
| Opis izdelka | VX Modular enclosure, WHdepth 600x2000x800 mm, sheet steel |
|--------------|--|

Approvals

| | |
|--------------|----------------|
| Certificates | Surface finish |
|--------------|----------------|

| | |
|--------------|------------------------------|
| Explanations | Declaration of conformity UK |
|--------------|------------------------------|