

# Rittal – The System.

Faster – better – everywhere.



## AS 4050.061 Upínací rám

State: 30.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.061 - Upínací rám

Parallel machining of enclosures in the cube machining zone of Perforex machining centres BC and Perforex milling terminals MT for shorter setup times and enhanced productivity.

## Features

Obj. č.	AS 4050.061
Prevedenie	Pneumatické upínacie zariadenie
Possible number of terminal Boxes for parallel processing	4
Poznámka	Použitie upínacieho rámu (obj. č. 4050.080) pri obrábacom centre BC (obj. č. 4050.230) je možné iba pri dvojdverovom variante.
Vhodný pre obj. č.	4050.107 4050.108 4050.230 4055.920 4055.921 4055.925 4055.926
Suitable for	Perforex BC 1007 HS Perforex BC 1008 HS Perforex BC 2014 HS Perforex MT 2101 Perforex MT 2101 S Perforex MT 2201 Perforex MT 2201 S
Rozmery upnutelných kompaktných skriň max.	Šírka: 200 mm Výška: 300 mm Hĺbka: 300 mm
Rozmery upnutelných kompaktných skriň min.	Šírka: 90 mm Výška: 70 mm Hĺbka: 70 mm
Balenie	1 pc(s).
Netto hmotnosť	25 kg

# Features

Brutto hmotnosť	25 kg
Číslo colnej sadzby	84669360
ETIM 9	EC003010
ETIM 8	EC003010
ECLASS 8.0	36609190
Popis výrobku	Upevňovací rám BC 1007/1008/2014, kompakt min. 200 x 300 x 300 mm