

Rittal – The System.

Faster – better – everywhere.



AS 4050.887

Závitová fréza

State: 27.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.887 - Závitová fréza

Milling cutter for cutting metric threads for Perforex machining centres BC and Perforex milling terminals MT.

Features

Obj. č.	AS 4050.887
Technické údaje	Priemer drieku 12 mm Priemer rezu 10 mm Stúpanie 1,5 mm Uhol úkosu 60° Rezná dĺžka 20 mm Celková dĺžka 85 mm
Pre závit	M12 - M64
Normy	DIN 13-1 metrický závit ISO
Obrobiteľný materiál	Steel Stainless steel Cast aluminium Plastic Copper
Balenie	1 pc(s).
Netto hmotnosť	0,124 kg
Brutto hmotnosť	0,124 kg
Číslo colnej sadzby	82077031
ETIM 9	EC000945
ETIM 8	EC000945
ECLASS 8.0	36609211
Popis výrobku	Fréza na kruhové závit, 10x1,5, 12mm