


Rittal – The System.

Faster – better – everywhere.



AS 4051.020

Krimpovací poloautomat RC-I

State: 23.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.020 - Krimpovací poloautomat RC-I pre Wire Terminal WT 24/36

Crimping machine with 5-way magazine for processing insulated wire end ferrules on a reel. This device has an interface to communicate with the Rittal Wire Terminal fully automated wire processing machine and supports complete functional integration. Training course 5058.207 must additionally be purchased for this item.



Features

Obj. č.	AS 4051.020
Výhody	Vďaka päťnásobnému osadeniu nie je nutná výmena izolovaných dutiniek
Technické údaje	Rozsah krimpovania 0,5 – 2,5 mm ² (AWG 20 – 14) Krimpovacia dĺžka 8 a 10 mm Zavádzacia dĺžka 27 mm (1,06 in.)
Vhodný pre obj. č.	4051024 4051036
Balenie	1 pc(s).
Netto hmotnosť	22 kg
Brutto hmotnosť	22,5 kg
Číslo colnej sadzby	84633000
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	17130101

Features

Popis výrobku

AS krimpovací stroj RC-I, elektropneumatický krimpovací stroj s 5-násobným zásobníkem na spracovanie izolovaných dutiniek na kotúči. Náš krimpovací stroj bol optimalizovaný a prispôsobený špeciálne pre plne automatický proces dutinkovania. De