

# Rittal – The System.

Faster – better – everywhere.



## AS 4054.030

## Krimповacie kliešte Flex

State: 2.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4054.030 - Krimpovacie kliešte Flex pre dutinky

For use with wire end ferrules with no insulating collar to DIN 46228, Part 1 and wire end ferrules with insulating collar to DIN 46228, Part 4.



## Features

Obj. č.	AS 4054.030
Prevedenie	priame
Výhody	Čelné alebo bočné pripevnenie izolovanej dutinky pomocou otočnej hlavy Minimálna vynaložená sila pri veľkých prierezoch vodičov Stabilne vysoko kvalitné lisovanie Uvoľniteľná západka Samoregulačné
Materiál	Vysoko kvalitná špeciálna nástrojová oceľ
Povrch	Potiahnuté, matná čierna farba
Farba	Rukoväť: antracitová a Rittal Power Pink
Lisovanie	Trapezoid crimp
Smer zavedenia kábla	čelné a bočné
Rozmery	Dĺžka: 180 mm
Prierez	26 - 8
Pre prierez	0,14 - 10 mm <sup>2</sup>
Balenie	1 pc(s).
Netto hmotnosť	0,35 kg
Brutto hmotnosť	0,388 kg

# Features

Číslo colnej sadzby	82032000
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811
Popis výrobku	Lisovacie kliešte AS pre prierez 0,14 -10 mm <sup>2</sup> , otočná hlava, lichobežníkové lisovanie