

Rittal – The System.

Faster – better – everywhere.



DK 5302.202

**Panel na pretiahnutie káblov s
kefovou lištou**

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5302.202 - Panel na pretiahnutie káblov s kefovou lištou 482,6 mm (19")

With cut-out 390 x 60 mm when using two opposite panels (2 U) or 390 x 30 mm for one panel (1 U) with brush insert.



Features

Obj. č.	DK 5302.202
Výhody	Pre zväčšenie káblvej priechodky je možné jednoducho vzájomne kombinovať dva panely
Oblasti použitia	Na uzavretie káblvého vedenia a súčasného káblvého vedenia v priestore montáže v 1 U, 482,6 mm (19") montážny štandard
Materiál	Oceľový plech Kefová lišta: plast, UL 94-HB, bez obsahu halogénu Vláčna kefovej lišty: plast PA6, bez obsahu halogénu Upevňovací korpus kefovej lišty: plast PVC, obsahujúci halogény
Povrch	S nástrekom
Farba	RAL 9005
Montážny výrez	Šírka:390 mm Výška:30 mm
Rozmery	Šírka: 482,6 mm
Výškové moduly	1 U
Balenie	1 pc(s).
Netto hmotnosť	0,2 kg
Brutto hmotnosť	0,243 kg

Features

PCF per pack (cradle-to-gate)	0,9 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	73269098
ETIM 9	EC000322
ECLASS 8.0	27400604
Popis výrobku	Káblový vstup s kefovou lištou, 1 U, 482,6 mm (19"), ocelový plech, RAL 9005