

Rittal – The System.

Faster – better – everywhere.



IW 6900.740

Priemyselné pracovné stanice

State: 27.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IW 6900.740 - Priemyselné pracovné stanice

Lower enclosure section, based on VX SE for Industrial Workstations.



Features

Obj. č.	IW 6900.740
Prevedenie	Pracovná doska, zásuvná priehradka na klávesnici, designové dvere, zadné dvere
Materiál	Skriňa, zásuvná priehradka na klávesnicu, designové dvere, zadné dvere: ocelový plech Pracovná doska: drevotriesková doska - po oboch stranách plastové laminovanie (po obvode nalepené hrany)
Povrch	Skriňa: základná farba nanosená máčaním, z vonkajšej strany štruktúrovaná prášková farba
Farba	Dekoratívne kryty: RAL 7015
Rozsah dodávky	Skriňa po stranách uzavretá Podlahové plechy, trojdielne Nivelačné nohy Pracovná doska, zásuvná priehradka na klávesnici, designové dvere, zadné dvere Pracovná doska, ŠxVxH 610 x 38 x 645 mm
Rozmery	Šírka: 600 mm Výška: 1.000 mm Hĺbka: 645 mm

Features

Stupeň krytia IP podľa normy IEC 60 529	IP 54
Rozmer s pracovnou doskou	Šírka: 610 mm Výška: 1.043 mm Hĺbka: 645 mm
Balenie	1 pc(s).
Netto hmotnosť	71 kg
Brutto hmotnosť	74 kg
PCF per pack (cradle-to-gate)	281,9 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	94032080
ETIM 9	EC002502
ETIM 8	EC002502
ECLASS 8.0	27180501
Popis výrobku	IW Industrial Workstation, skriňa, ŠxVxH: 600x1000x645 mm, s pracovnou doskou, zásuvka na klávesnicu, dizajnové dvere vpredu, zadné dvere

Approvals

Certificates	Surface finish
Explanations	Declaration of conformity