

Rittal – The System.

Faster – better – everywhere.



TS 8806.580

Povezovalni sistemi TS 8

State: 25.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8806.580 - Povezovalni sistemi TS 8 IP 66/NEMA 4

Baying systems TS 8, protection category IP 66, NEMA 4, sheet steel, spray-finished

Features

Št. Modela	TS 8806.580
Material	Okvir ohišja: jeklena pločevina, 1,5 mm Streha: jeklena pločevina, 1,5 mm Vrata: jeklena pločevina, 2,0 mm Zadnja plošča: jeklena pločevina, 1,5 mm Osnova: jeklena pločevina, 1,5 mm Montažna plošča: jeklena pločevina, 3,0 mm
Površinska obdelava	Okvir ohišja, vrata, streha in zadnja plošča: temeljni premaz in prašno barvano, teksturirana barva Montažna plošča: pocinkana
Barva	RAL 7035
Obseg dobave	Okvir ohišja Vrata Vrata s tečaji na desni, možnost menjave na levo Strešna plošča Podnožje, zaprto Zadnja plošča Montažna plošča 4 očesni vijaki Ključavnica: 3 mm dvojna ključavnica 2 luknjani tirnici TS 18 x 38 mm 2 podporna trakova, nameščena v globino ohišja Komplet dodatne opreme za stranske plošče za nadgradnjo na IP 66
Mere	Širina: 800 mm Višina: 2.000 mm Globina: 600 mm
Mere montažne plošče (Š x V)	699 mm x 1.896 mm
Razred zaščite po IEC 60 529	IP 66

Features

Razred zaščite NEMA	NEMA 1 NEMA 4 NEMA 12
Tipaska ocena po UL 50E	Type 1 Type 4 Type 12
IK koda	IK09
Osnovni material	Sheet steel
Paketi	1 pc(s).
Neto teža	123,975 kg
Bruto teža	131,4 kg
Carinska tarifna številka	94032080
ETIM 9	EC000261
ECLASS 8.0	27180101
Opis izdelka	TS Bayed enclosure system, WHD: 800x2000x600 mm, Sheet steel, IP 66 / NEMA 4, with mounting plate, single door at the front

Approvals

Approvals	Bureau Veritas C-UL DNV UL + C-UL (listed)
Certificates	Surface finish
Explanations	Manufacturer's declaration Declaration of conformity Declaration of conformity UK