## Rittal – The System.

Faster – better – everywhere.





## VX 8828.000 Bayed enclosure system VX25

State: 1.11.2025 (Source: rittal.com/si-sl)



# VX 8828.000 - Bayed enclosure system VX25 Basic enclosure

The standard in enclosure manufacturing: Enclosure frame with one or two front doors, rear panel, mounting plate, roof plate, divided gland plates. Perfectly suited to efficient enclosure interior installation.







#### **Features**

Model No.	VX 8828.000
Material	Enclosure frame: Sheet steel, 1.5 mm
	Roof: Sheet steel, 1.5 mm
	Door: Sheet steel, 2.0 mm
	Rear panel: Sheet steel, 1.5 mm
	Gland plates: Sheet steel, 1.5 mm
	Mounting plate: Sheet steel, 3.0 mm
Surface finish	Enclosure frame: Dipcoat-primed
	Door, roof and rear panel: Dipcoat-primed, powder-coated on the
	outside, textured paint
	Mounting plate and gland plates: Zinc-plated
Colour	RAL 7035

© Rittal 2025 2

#### **Features**

Supply includes	Enclosure frame
	Door(s)
	Door hinged on the right, may be swapped to the left
	Roof plate Rear panel
	Gland plates
	Mounting plate
	2 punched rails 18 x 39 mm
	Lock: 3 mm double-bit
Dimensions	Width: 800 mm
	Height: 2,200 mm
	Depth: 800 mm
Dimensions mounting plate (W x H)	699 mm x 2,096 mm
Protection category to IEC 60 529	IP 55
Protection category NEMA	NEMA 12
Type rating to UL 50E	Type 1
	Type 12
IK Code	IK10
Number of doors	1
Basic material	Sheet steel
Packs of	1 pc(s).
Net weight	298.501
Gross weight	323.633
PCF per pack (cradle-to-gate)	362.2 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	8421399090
EAN	4028177935990
EAN11 (UC)	94010
ETIM 9	EC000261

© Rittal 2025 3

### Features

ETIM 8	EC000261
ECLASS 8.0	27180101

## **Approvals**

Approvals	UL + C-UL (listed)
Certificates	Surface finish
Explanations	Manufacturer's declaration
	Declaration of conformity
	Declaration of conformity UK
	PCF-declaration

© Rittal 2025