

Rittal – The System.

Faster – better – everywhere.



RX 9360.200

RiLineX connection adaptor

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.200 - RiLineX connection adaptor

RiLineX connection adaptor for 60 mm busbar systems. The adaptor boasts an impressive compact design and simple conductor connection. Dismantling requires the use of tools. Round conductors may be connected either from above or below. The push-in connection clamps are designed for easier connection. Mounted by simply snapping onto the RiLineX board. The connection adaptor features a high current-carrying capacity plus high levels of short-circuit protection and universal contact hazard protection that adapts to the relevant wire gauge. The device features semi-automatic adjustment of the busbar thickness between 5 and 10 mm.



Features

| | |
|---------------------------------------|--|
| Obj. č. | RX 9360.200 |
| Výhody | Mounting on the busbar system and cable connection with just one screw |
| Materiál | Polyamid (PA 6) Ochrana proti požiaru zodpovedá UL 94 |
| Farba | RAL 9005 |
| Menovitý prúd (max.) | 67 A |
| Menovitý prúd max. | 76 A |
| Rated current of round conductor | 76 A |
| Rated current of round conductor (UL) | 66 A |

Features

| | |
|---|--|
| Elektrické parametre UL (SCCR) | 5 kA - 600 V, RMS 35 kA - 480 V, circuit breaker max. 60 A, DIVQ/7 100 kA - 600 V, Fuse Class J max. 100 A, JDDZ/7 |
| Vývod vodičov | Top/bottom |
| Pre prípojnicové systémy s rozstupom | 60 mm |
| Počet pólov | 3-pole |
| Vhodné pre prípojnicový systém | RiLineX RiLine60 |
| Rozmery | Šírka: 26,8 mm Výška: 239,2 mm Hĺbka: 103,3 mm |
| Pripojenie okrúhlych vodičov | 1,5 - 16 mm ² |
| Vhodné pre prípojnice | 15 x 5/10 20 x 5/10 30 x 5/10 |
| Rated voltage | 800 V AC 800 V DC 600 V AC (UL) 600 V DC (UL) |
| Trieda prepätia | 4 |
| Stupeň znečistenia | 3 |
| Normy | IEC/EN 61439-1 UL 508 |
| Menovité rázové napätie Uimp | 8 kV |
| Rated insulation voltage Ui | 800 V |
| Stratový výkon max. | 7 W |
| Stupeň krytia IP podľa normy IEC 60 529 | IP 2XB |
| Maximum operating air humidity | 90 % |
| Rozsah prevádzkových teplôt | -5 °C...55 °C |

Features

| | |
|----------------------------------|--|
| Rozsah skladovacích teplôt | -25 °C...75 °C |
| Vlhkosť vzduchu (nekondenzujúca) | 10...90 % |
| Pre hrúbku prípojníc | 1,5 - 16 mm |
| Balenie | 4 pc(s). |
| Netto hmotnosť | 1,2 kg |
| Brutto hmotnosť | 1,656 kg |
| PCF per pack (cradle-to-gate) | 13,4 |
| Číslo colnej sadzby | 85369010 |
| ETIM 9 | EC001531 |
| Popis výrobku | RiLineX connection adaptor for 60 mm busbar systems. The adaptor boasts an impressive compact design and simple conductor connection. Dismantling requires the use of tools. Round conductors may be connected either from above or below. The push-in connection clamps are designed for easier connection. Mounted by simply snapping onto the RiLineX board. The connection adaptor features a high current-carrying capacity plus high levels of short-circuit protection and universal contact hazard protection that adapts to the relevant wire gauge. The device features semi-automatic adjustment of the busbar thickness between 5 and 10 mm. |

Approvals

| | |
|--------------|--|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity PCF-declaration |