

Rittal – The System.

Faster – better – everywhere.



RX 9360.824

RiLineX fuse-switch disconnecter

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.824 - RiLineX fuse-switch disconnecter D-Switch

RiLineX fuse-switch disconnecter for 60 mm busbar systems. For use with D 01 (via gauge ring) and D 02 slow fuses (max. 63 A). Also for use with 10 x 38 mm cylindrical fuses via the supplied retaining springs. Integral optical LED fuse monitoring plus electronic fuse monitoring with alarm contacts The switch is lockable in the on and off positions. Spring terminal blocks up to 16 mm² at an angle of 45° enable easier conductor connection. The device is suitable for tool-free snap-on mounting with semi-automatic busbar adjustment for 5 and 10 mm.



Features

Obj. č.	RX 9360.824
Výhody	Reliable contacting of fuse inserts (without screw caps) Snap-on mounting and simple adjustment for busbar thickness (5/10 mm) Optical LED fuse monitoring Voltage test through separate opening Maintenance-free tension spring connection up to 16 mm ² Complete contact hazard protection without any additional accessories (such as screw caps)
Materiál	Polyamid (PA 6) Ochrana proti požiaru zodpovedá UL 94
General colour	RAL 35745 RAL 9005
Rozsah dodávky	4 fuse-switch disconnectors 12 reducers for D 01 fuses
Spôsob (elektrického) pripojenia	Spring terminal

Features

Menovitý prúd max.	63 A
Menovité prevádzkové napätie	400 V AC
Vývod vodičov	Bottom
Počet pólov	3-pole
Vhodné pre prípojnicový systém	RiLineX RiLine60
Rozmery	Šírka: 35,8 mm Výška: 263 mm Hĺbka: 104,2 mm
Vhodné pre prípojnice	15 x 5/10 20 x 5/10 30 x 5/10
Trieda prepätia	4
Stupeň znečistenia	3
Normy	IEC/DIN EN 60 947-3
Rated insulation voltage Ui	800 V
Stratový výkon max.	5,5 W
Stupeň krytia IP podľa normy IEC 60 529	IP 2XB
Maximum operating air humidity	90 %
Rozsah prevádzkových teplôt	-5 °C...55 °C
Rozsah skladovacích teplôt	-25 °C...75 °C
Vlhkosť vzduchu (nekondenzujúca)	10...90 %
Utilisation category	AC-22B (400 V/100 A)
Poistkové vložky	D 02-E 18
Balenie	4 pc(s).
Netto hmotnosť	2,232 kg
Brutto hmotnosť	2,236 kg
Podiel medi (kg / ks)	0,105

Features

PCF per pack (cradle-to-gate)	14,81
Číslo colnej sadzby	85365080
ETIM 9	EC001040
Popis výrobku	RiLineX fuse-switch disconnecter for 60 mm busbar systems. For use with D 01 (via gauge ring) and D 02 slow fuses (max. 63 A). Also for use with 10 x 38 mm cylindrical fuses via the supplied retaining springs. Integral optical LED fuse monitoring plus electronic fuse monitoring with alarm contacts The switch is lockable in the on and off positions. Spring terminal blocks up to 16 mm ² at an angle of 45° enable easier conductor connection. The device is suitable for tool-free snap-on mounting with semi-automatic busbar adjustment for 5 and 10 mm.

Approvals

Explanations	Declaration of conformity PCF-declaration
--------------	--